


Bergmannstrasse 10
 88471 Laupheim/Germany
 Phone +49 (0)7392/97 25-0
 Fax +49 (0)7392/97 25-50
 Email info@pernuma.de
 Web www.pernuma.de



PERNUMA PERFOSET I/D, II/D Date Perforating Machines

**for marking forms, labels, films or packagings
 by a date or by changeable letter and/or
 number combinations**

The machines are supplied with 18 figure slides for a 6 digits date in their standard version.

These so-called slides are small metal sticks which can very fast and easily be inserted into/respectively pulled out of the machine from the front of it.

There are two hand-operated machines in our manufacturing programme as described below:

PERNUMA PERFOSET I/D

Up to 15 sheets of 70 g/m² paper can be perforated in one operation.

The insertion depth is 75 mm (from the paper margin up to the middle of the impression).

Instead of a date the machine is available with an arbitrary number of digits in one line (letters or figures) within a max. width of 60 mm.

PERNUMA PERFOSET II/D

Up to 25 sheets of 70 g/m² paper can be perforated in one operation.

The insertion depth is 110 mm (from the paper margin up to the middle of the impression).


Instead of a date the machine is available with an arbitrary number of digits in one line (letters or figures) within a max. width of 88 mm.

The standard figure heights are 6, 8 or 10 mm.

Both models are equipped with an adjustable side and rear gauge in order to facilitate an exact positioning of the perforation.



Bergmannstrasse 10
88471 Laupheim/Germany
Phone +49 (0)7392/97 25-0
Fax +49 (0)7392/97 25-50
Email info@pernuma.de
Web www.pernuma.de



PERNUMA PERFOSET I/D, II/D Date Perforating Machines

These machines are available also

- with an additional fixed text line above or below the slide device (with PERFOSET I/D in 6 or 8 mm height only).
Our model PERFOSET II/D can be equipped with an additional text line above as well as below the date.
- with a safety lock preventing unauthorized persons from working with the machine.

Technical Data

PERNUMA PERFOSET	I/D	II/D
Insertion depth	75 mm	110 mm
Net weight	6.7 kg	12.2 kg
Gross weight	7.5 kg	13.5 kg

Packaging dimensions:

Perfoset I/D	43 x 34 x 20 cm
Perfoset II/D	52 x 33 x 23 cm



Figure height 6 mm, pin Ø 0.8 mm



Figure height 8 mm, pin Ø 0.9 mm



Figure height 10 mm, pin Ø 1.1 mm

Technical Data and design subject to change.
PERFOSET I/D, II/D - E - 01/06

